



# COATING LIST and MEDICAL FILTER

Product name		USC-ES BD	USC, USC-BC USC-ES, USC-ESBC	MSC MSC-P	ESC-P	ESC+ BCC-P	SPS SPS-P	PGC-P	PGC	BCC-P	TBC TBC-P	NCC	DFC	RMC	Mirror	Color AR	HADABIJIN-P	ESC+ HADABIJIN-P	CLC/ CCP/ CCP400	Actiview	
LUTINA	LTN 1.76 NEUROGRAN	X	X	X	X	X	X			X	X			X							
	LTN 1.67 NEUROGRAN	X	X	X	X	X	X	X	X	X	X			X	X		X	X		X	
	LTN 1.60 NEUROGRAN	X	X	X	X	X	X	X	X	X	X		X	X	X	X	X	X		X	
	LTN 1.76 GR-RESONAS (MTi / i / MT)	X	X	X	X	X	X			X	X			X							
	LTN 1.67 GR-RESONAS (MTi / i / MT)	X	X	X	X	X	X	X	X	X	X			X	X		X	X		X	
	LTN 1.60 GR-RESONAS (MTi / i / MT)	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X		X	
	LTN 1.76 RESONAS-X	X	X	X	X	X	X			X	X				X						
	LTN 1.67 RESONAS-X	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 RESONAS-X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.76 RESONAS WS (MT) / FIT WS (MT) / PRESSO WS (MT)	X	X	X	X	X	X			X	X				X						
	LTN 1.67 RESONAS WS (MT) / FIT WS (MT) / PRESSO WS (MT)	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 RESONAS WS (MT) / FIT WS (MT) / PRESSO WS (MT)	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.76 NWS	X	X	X	X	X	X			X	X				X						
	LTN 1.67 NWS	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 NWS	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.76 RESONAS (MT) / FIT (MT) / PRESSO (MT)	X	X	X	X	X	X			X	X				X						
	LTN 1.67 RESONAS (MT) / FIT (MT) / PRESSO (MT)	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 RESONAS (MT) / FIT (MT) / PRESSO (MT)	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.76 SERENO IS	X	X	X	X	X	X			X	X				X						
	LTN 1.67 SERENO IS	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 SERENO IS	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.67 ENERGY	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 ENERGY	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.76 BS-INDOOR	X	X	X	X	X	X			X	X				X						
	LTN 1.67 BS-INDOOR	X	X	X	X	X	X	X	X	X	X				X			X	X		X
	LTN 1.60 BS-INDOOR	X	X	X	X	X	X	X	X	X	X			X			X	X	X		X
	LTN 1.76 LARGO WS / BS-LARGO	X	X	X	X	X	X			X	X				X						
	LTN 1.67 LARGO WS / BS-LARGO	X	X	X	X	X	X	X	X	X	X				X			X	X		X
	LTN 1.60 LARGO WS / BS-LARGO	X	X	X	X	X	X	X	X	X	X			X			X	X	X		X
	LTN 1.76 REST W	X	X	X	X	X	X			X	X				X						
	LTN 1.67 REST W	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 REST W	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.76 REST R	X	X	X	X	X	X			X	X				X						
	LTN 1.67 REST R	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 REST R	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.76 CVf	X	X	X	X	X	X			X	X				X						
	LTN 1.67 CVf	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 CVf	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.76 Bi-AS(S) / (C) & 1.76GO	X	X	X	X	X	X			X	X				X						
	LTN 1.67 Bi-AS(S) / (C) & 1.67GO	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 Bi-AS(S) / (C) & 1.60GO	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.76 AS	X	X	X	X	X	X	X	X	X	X				X						
	LTN 1.67 AS	X	X	X	X	X	X	X	X	X	X				X	X		X	X		X
	LTN 1.60 AS	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
	LTN 1.60	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X
LUTINA PHOTOCROMIC	LTN 1.76 NEUROGRAN			MSC-P					X	X											
	LTN 1.67 NEUROGRAN			MSC-P					X	X											
	LTN 1.60 NEUROGRAN			MSC-P					X	X											
	LTN 1.76 GR-RESONAS & LTN 1.76 MT GR-RESONAS			MSC-P					X	X											
	LTN 1.67 GR-RESONAS & LTN 1.70 MT GR-RESONAS			MSC-P					X	X											
	LTN 1.60 GR-RESONAS & LTN 1.60MT GR-RESONAS			MSC-P					X	X											
	LTN 1.76 RESONAS (MT)			MSC-P					X	X											
	LTN 1.67 RESONAS (MT)			MSC-P					X	X											
	LTN 1.60 RESONAS (MT)			MSC-P					X	X											
	LTN 1.76 REST W			MSC-P					X	X											
	LTN 1.67 REST W			MSC-P					X	X											
	LTN 1.60 REST W			MSC-P					X	X											
	LTN 1.76 REST R			MSC-P					X	X											
	LTN 1.67 REST R			MSC-P					X	X											
	LTN 1.60 REST R			MSC-P					X	X											
	LTN 1.76 Bi-AS(S) / (C)			MSC-P					X	X											
LTN 1.67 Bi-AS(S) / (C)			MSC-P					X	X												
LTN 1.60 Bi-AS(S) / (C)			MSC-P					X	X												
LTN 1.76 AS			MSC-P					X	X												
LTN 1.67 AS			MSC-P					X	X												
LTN 1.60 AS			MSC-P					X	X												



P-UV(- P) : Protection Ultraviolet  
EX. MSC-P = MSC plus P-UV is available.



# COATING LIST and MEDICAL FILTER

Product name		USC-ES BD	USC, USC-BC USC-ES, USC-ESBC	MSC MSC-P	ESC-P	ESC+BC-P	SPS SPS-P	PGC-P	PGC	BCC-P	TBC TBC-P	NCC	DFC	RMC	Mirror	Color AR	HADABUN-P	ESC+ HADABUN-P	CLC/ CCP/ CCP400	Actiview	HC	
DOUBLE-SIDE PAL	1.76 NEUROGRAN	X	X	X	X	X	X		X	X	X	X		X								
	1.70 NEUROGRAN	X	X	X	X	X	X	X	X	X	X	X		X	X		X	X			X	
	1.60 NEUROGRAN	X	X	X	X	X	X	X	X	X	X	X		X	X	X	X	X	X		X	
	1.76 GR-RESONAS (MT) / i / (MT)	X	X	X	X	X	X	X		X	X	X		X								
	1.70 GR-RESONAS (MT) / i / (MT)	X	X	X	X	X	X	X	X	X	X	X			X	X		X	X		X	
	1.60 GR-RESONAS (MT) / i / (MT)	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	
	1.76 RESONAS-X	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X		X	
	1.70 RESONAS-X	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X		X	
	1.60 RESONAS-X	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X		X	
	1.76 RESONAS WS (MT) / FIT WS (MT) / PRESSO WS (MT)	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X		X	
	1.70 RESONAS WS (MT) / FIT WS (MT) / PRESSO WS (MT)	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X		X	
	1.60 RESONAS WS (MT) / FIT WS (MT) / PRESSO WS (MT)	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	
BACK-SIDE PAL	1.76 NWS	X	X	X	X	X	X		X	X	X			X								
	1.70 NWS	X	X	X	X	X	X	X	X	X	X			X	X		X	X			X	
	1.60 NWS	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X		X	
	1.76 RESONAS (MT) / FIT (MT) / PRESSO (MT)	X	X	X	X	X	X	X	X	X	X			X	X		X	X			X	
	1.70 RESONAS (MT) / FIT (MT) / PRESSO (MT)	X	X	X	X	X	X	X	X	X	X			X	X		X	X			X	
	1.60 RESONAS (MT) / FIT (MT) / PRESSO (MT)	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
	1.50 RESONAS (MT) / FIT (MT) / PRESSO (MT)								X	X	X			X	X	X	X	X			X	
	1.76 SERENO IS	X	X	X	X	X	X	X		X	X	X			X			X	X			X
	1.70 SERENO IS	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X
	1.60 SERENO IS	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X
	1.50 SERENO IS								X	X	X			X	X	X	X	X	X			X
	PAL	1.70 ENERGY	X	X	X	X	X	X	X	X	X	X			X	X		X	X			X
1.60 ENERGY		X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
1.50 ENERGY									X	X	X			X	X		X	X			X	
1.70 BS-C / -PM 9MM / -PM / -13,15		X	X	X	X	X	X	X	X	X	X			X	X		X	X			X	
1.60 BS-C / -PM 9MM / -PM / -13,15		X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
1.50 BS-C / -PM / -13,15									X	X	X			X	X		X	X			X	
1.70 SERENO NEX / PM 11,13		X	X	X	X	X	X	X	X	X	X			X	X		X	X			X	
1.60 SERENO NEX / PM 11,13		X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
1.50 SERENO NEX / PM 11,13									X	X	X			X	X	X	X	X			X	
INDOOR		1.76 BS-INDOOR	X	X	X	X	X	X		X	X	X			X			X	X			X
		1.70 BS-INDOOR / INDOOR NEX / INDOOR	X	X	X	X	X	X	X	X	X	X			X			X	X			X
		1.60 BS-INDOOR / INDOOR NEX / INDOOR	X	X	X	X	X	X	X	X	X	X			X			X	X			X
	1.50 BS-INDOOR / INDOOR NEX / INDOOR								X	X	X			X			X	X			X	
	WIDE VISION	1.76 LARGO WS / BS-LARGO	X	X	X	X	X	X		X	X	X			X			X	X			X
1.70 LARGO WS / BS-LARGO / LARGO NEX / LARGO		X	X	X	X	X	X	X	X	X	X			X			X	X			X	
1.60 LARGO WS / BS-LARGO / LARGO NEX / LARGO		X	X	X	X	X	X	X	X	X	X			X			X	X			X	
1.50 BS-LARGO / LARGO NEX / LARGO									X	X	X			X			X	X			X	
EYE ASSIST		1.76 REST W	X	X	X	X	X	X		X	X	X			X			X	X			X
	1.70 REST W	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
	1.60 REST W	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
	1.76 REST R	X	X	X	X	X	X		X	X	X			X			X	X			X	
	1.70 REST R / REST S / SUPPLE PLUS	X	X	X	X	X	X	X	X	X	X			X	X		X	X			X	
	1.60 REST R / REST S / SUPPLE PLUS	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
SINGLE VISION	1.76 CVI / 1.76 Bi-AS (S) / (C) & 1.76 GO	X	X	X	X	X	X		X	X	X			X			X	X			X	
	1.70 CVI(Except CMC) / 1.70 Bi-AS (S) / (C)	X	X	X	X	X	X	X	X	X	X			X	X		X	X			X	
	1.67 GO	X	X	X	X	X	X		X	X	X			X	X		X	X			X	
	1.60 CVI(Except CMC) / 1.60 Bi-AS (S) / (C)	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
	1.60 GO	X	X	X	X	X	X		X	X	X			X	X	X	X	X			X	
	1.76AS	X	X	X	X	X	X		X	X	X			X	X		X	X			X	
	1.70AS	X	X	X	X	X	X	X	X	X	X			X	X		X	X			X	
	1.60AS	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
	1.60	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X			X	
	1.50								X	X	X			X	X		X	X			X	
	FUNCTIONAL LENS	1.60 BFC25 / 28							X	X	X				X							X
		1.60 GF16							X	X	X				X							X
1.76 MODECINQ PAL / MODECINQ		X	X	X	X	X	X		X	X	X			X			X	X			X	
1.70 MODECINQ PAL / MODECINQ		X	X	X	X	X	X	X	X	X	X			X			X	X			X	
1.60 MODECINQ PAL / MODECINQ		X	X	X	X	X	X	X	X	X	X			X			X	X			X	
1.60 POLAR / POLAR MODECINQ GY / BR									X					X	X		X	X			X	
1.60 POLAR BS-C / -PM / -11,13,15,17 GY / BR									X					X	X		X	X			X	
1.50 POLAR LGY/DGY / LBR / DBR / DGN														X	X		X	X			X	
PGC / RMC / HMC & ★ HC / UNC									X						X							X
TR 1.76 GR-RESONAS GY / BR									X						X							X
TR 1.76 RESONAS WS / FIT WS GY / BR									X	X					X							X
TR 1.76 / 1.70 / 1.60 RESONAS (MT) / FIT (MT) GY / BR									X	X					X							X
TR-XA 1.60 RESONAS (MT) / FIT (MT)								X	X					X							X	
TR 1.60 BS-PM 9MM GY / BRTR-XA 1.60 BS-PM 9MM								X	X					X							X	
TR 1.50 RESONAS GY / BR								X	X					X							X	
TR 1.76 GO / 1.70AS / 1.60 GY / BRTR-XA 1.60								X	X					X							X	
1.60 PHOTO BS-C / -PM / -11,13,15 GY / BR								X	X					X							X	
1.60 NIGHT DRIVE PAL								X						X							X	
1.60 NIGHT DRIVE / 1.60AS NIGHT DRIVE								X						X							X	
1.60 GOLF 50								SPS														
1.60 SPORT6 / SPORT8								X	X					X	X	X				SPORT8	X	

Product name		PGC	MC	PGC - LTN	MC - LTN
PAL	G1.90 PM / G1.80 PM	X	X	X	X
BIF	G1.60 BFC25	X	X		
BIF	G1.50 BFC25 / G1.50 BFC28	X	X		
BIF	G1.50 BFC25BX	X	X		
SV	G1.90 AS / G1.80 AS G1.90 / G1.80 / G1.70 / G1.60	X	X	X	X
SV	G1.50 PGX / PBX	X	X		



P-UV ( - P ) : Protection Ultraviolet  
EX. MSC-P = MSC plus P-UV is available.

